

AZM



| Model | Length | Number of magnets |
|---------|--------|-------------------|
| AZM 30 | 30 cm | 2 |
| AZM 40 | 40 cm | 2 |
| AZM 50 | 50 cm | 4 |
| AZM 60 | 60 cm | 4 |
| AZM 80 | 80 cm | 4 |
| AZM 100 | 100 cm | 6 |
| AZM 120 | 120 cm | 6 |
| AZM 150 | 150 cm | 8 |
| AZM 180 | 180 cm | 8 |
| AZM 200 | 200 cm | 8 |



CHARACTERISTICS:

- Better, faster, and more accurate reading through the patented SOLA FOCUS vials
- Improved readability in dim light thanks to optimized SOLA luminous backing
- Outstanding measuring accuracy in standard and inverted position
- Lateral magnet installation for a seamless measuring surface and maximum protection of the magnet
- Strong neodymium magnet for high adhesive force
- Shock-absorbing end caps

APPLICATIONS:

- Horizontal measurement
- Vertical measurement

Technical details:

| | |
|---|--------------------------|
| Item description | Box profile spirit level |
| Dimensions | 50 x 24 mm |
| Material | Aluminum |
| Surface | anodized |
| Color | gold |
| Profile weight | 750 g/m |
| Measuring tolerance, standard position | 0.50 mm/m (0.029°) |
| Measuring tolerance, inverted measurement | 0.75 mm/m (0.043°) |
| Number of horizontal vials | 1 |
| Number of vertical vials | 1 |
| Measuring surface | anodized |
| Magnet | Neodymium |
| End cap | 1-c |
| Magnet | Yes |